

# C-Profile

## Robust steel profiles for versatile applications

Our galvanised steel C-profiles offer a reliable solution for numerous indoor applications. They are characterised by high stability, durability and corrosion resistance. Manufactured to the highest industrial standards, our cold-rolled C-profiles guarantee consistent quality and precise dimensional accuracy.



### Product Specification

Profile Type	C-Profile, cold-rolled
Material	cold profile according to EN 10162:2003
Steel Grade	Hot-dip galvanised slit strip, grade DX 51D +Z 140 (min.), in accordance with EN 10162:2003 & EN 10143:2006
Application	Construction, substructure, support systems, fastening solutions
Properties	High dimensional accuracy. Effective corrosion protection low weight with high load capacity



### Standard Profile Dimension

C40 x 40 x2 mm	Lengths: 558, 2.399 mm, 6.000 mm
C50 x40 x3 mm	Lengths: 558, 2.399 mm, 6.000 mm
C65 x40 x2 mm	Lengths: 558, 2.399 mm, 6.000 mm
C80 x40 x2 mm	Lengths: 558, 2.399 mm, 6.000 mm
C105 x40 x2,5 mm	Lengths: 558, 2.399 mm, 6.000 mm

### Customised Solutions

On request, we can manufacture our C-profiles in different lengths to suit your individual requirements. Please feel free to contact us.



Please scan the QR code or click [here](#) to go to the current product page.



# Tate.

**Tate Global GmbH**

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: [infoDE@tateglobal.com](mailto:infoDE@tateglobal.com)

W: [tateglobal.com/de](http://tateglobal.com/de)

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-pedestal-c-profile-product-datasheet-en-de-v2 1/2026

