



Product Information

Product description

Water-dilutable, low emission and solvent-free impregnation concentrate for absorptive mineral substrates indoors.

Application range

Dust-binding impregnation especially designed for the installation of double / hollow-core flooring. Green, transparent impregnation concentrate 1:35.

Properties:

- Very low emission, solvent-free, plasticiser-free
- Free of fogging-active substances
- Emission class A+ (best possible value according to Construction Product Labelling Regulations (F))
- Good dust-binding effect
- Good compatibility with Tate pedestal adhesives

Instructions For Use

Substrate / Pretreatment

Suitable for mineral substrates. Substrates must be free of oils or other separation layers, dry and solid. Remove all cement slurry, sinter layers and/or separative substances. Preparation of sample areas is required in case of problematic substrates.

Application

Dilute Multikonzentrat grün with water at a mixing ratio of 1:35. Apply by brush or roller.

Technical Data

Composition

Polymer dispersion, water, additives, coloured pigment, preservatives.

Density, colour shade, container size

Density: approx. 10 g/cm³ / colour shade: green, transparent / container size: 1 l

Application

By brush, roller.

Application temperature

Ambient and substrate temperature: > +5°C. The relative air humidity must not exceed 80%.

Consumption rate

Diluted with water the prepared concentrate suffices for a surface of approx. 150 m². The exact consumption rate must be assessed by preparing sample areas. The consumption rate strongly depends on the substrate's absorbency.

Drying times

Accessible to pedestrians after approx. 5 hours at +20 °C and 65 % rel. air humidity.

Cleaning of tools

With water immediately after use. Store dry, cool but above freezing point. Storable for 12 months in original containers.

GISCODE

BSW20

VOC value

Cat. (A/h): 30 g/l (2010). This product contains < 1 g/l VOC.

Safety advice

For further information see current safety data sheet.

Disposal

Only recycle completely empty containers. Dried material residues can be disposed of as domestic waste; dispose of liquid residues at collection points for old paints.

All recommendations on the use of our products given to support buyers/users are based on our experience and correspond to the present state of knowledge in science and practical application. They are non-binding and shall substantiate neither a contractual legal relationship nor any secondary obligations under the contract of purchase. They do not exempt the customer from autonomously checking whether our products are suitable for the intended purpose. The general rules for structural engineering are to be complied with. We reserve the right to make changes that serve the purpose of technical progress or product improvement. With the publication of this technical data sheet all previous versions regarding this product are no longer valid. Version 06.12.2022



Tate.[®]

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

We reserve the right to change specification or design and supply products which may differ from those described and illustrated without notice and without liability.

tate-eco-multikonzentrat-gruen-datasheet-en-de-v2 4/2025



#planetpassionate