

Hollow Floor Pedestal M12

CLASS 5

- Bonding of the base plate to unfinished floors using Tate pedestal adhesive
- Top and bottom plates can be secured using a Tate pedestal adhesive
- Fix in place with Tate pedestal fixing adhesive as required



Pedestal	
Pedestal head	Top plate diameter 100 mm embossed Thickness 2 mm Pedestal tube 17 x 2 mm Tapered pedestal tube with thread M12 Top plate with tube centrally welded
Pedestal base	Base plate diameter 60 mm embossed Thickness 2.0 mm Threaded bolt M12 Base plate with threaded bolt centrally welded

Test Results According to DIN EN 13213:2001

Class	5
Nominal point load	5 kN
Ultimate load	≥ 10 kN
Depending on the respective Tate system	

Designation

F1 - SHB M12 - SH	35–57 mm
F2 - SHB M12 - SH	50–72 mm
F3 - SHB M12 - SH	60–97 mm
F4 - SHB M12 - SH	76–130 mm
F5 - SHB M12 - SH	110–170 mm
F6 - SHB M12 - SH	150–210 mm
Material	Steel, galvanised (transparent/bluish iridescent passivated)

The adjustment ranges mentioned must be observed



Please scan the QR code or click [here](#) to go to the current product page.



Tate®

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-pedestal-m12-product-datasheet-en-de-v3 4/2025



#planetpassionate