

# Raised Access Floor Pedestal M16-SG3

## CLASS 2

- Top plate with perforation diameter of approx. 6.6 and 3.5 mm for clip-on or screw-in stringers/cross bars
- Base plate with perforation diameter of approx. 7.0 mm for anchoring to unfinished floors
- Fix in the threaded bolt with Tate pedestal adhesive
- Bond to unfinished floors with Tate pedestal adhesive



| Pedestal      |                                                                                                                                                                                                      |
|---------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Pedestal head | <p>Top plate diameter 90 mm embossed<br/>Thickness 3 mm</p> <p>Pedestal tube 21,3x2 mm</p> <p>Tapered pedestal tube with<br/>thread M16</p> <p>Top plate with tube centrally<br/>welded</p>          |
| Pedestal base | <p>Base plate diameter 80 mm<br/>embossed Thickness 1.5 mm</p> <p>Threaded bolt M16<br/>(from DN-04/SG3 onwards<br/>with lock nut M16)</p> <p>Base plate with threaded bolt<br/>centrally welded</p> |

## Test Results DIN EN 12825:2002

|                                         |        |
|-----------------------------------------|--------|
| Class                                   | 2      |
| Nominal point load                      | 3 kN   |
| Ultimate load                           | ≥ 6 kN |
| Depending on the respective Tate system |        |

## Designation

|                      |                                                                    |
|----------------------|--------------------------------------------------------------------|
| DN-00/SG3-M16 SH 22  | 18–26 mm                                                           |
| DN-01/SG3-M16 SH 30  | 24–36 mm                                                           |
| DN-02/SG3-M16 SH 40  | 30–50 mm                                                           |
| DN-03/SG3-M16 SH 60  | 45–70 mm                                                           |
| DN-04/SG3-M16 SH 80  | 60–95 mm                                                           |
| DN-05/SG3-M16 SH 110 | 85–140 mm                                                          |
| DN-06/SG3-M16 SH 150 | 120–210 mm                                                         |
| DN-07/SG3-M16 SH 190 | 160–250 mm                                                         |
| Material             | Steel, galvanised<br>(transparent/bluish<br>iridescent passivated) |

The adjustment ranges mentioned must be observed



Please scan the QR  
code or click [here](#) to  
go to the current  
product page.



# Tate®

## Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: [infoDE@tateglobal.com](mailto:infoDE@tateglobal.com) W: [tateglobal.com/de](http://tateglobal.com/de)

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-pedestal-m16-sg3-product-datasheet-en-de-v3 4/2025



#planetpassionate