

Tate Approved Positile List 10/1/24

Any style or color outside this range must be approved by Shaw before the order will be accepted by Tate. For questions regarding approval of styles not listed below contact Anthony Taylor anthony.taylor@shawinc.com

1. Carpet must be textured loop. Cut pile is not acceptable.

2. Light colors with minimal or no pattern tend to telegraph the Positile buttons more than dark colors and busy patterns

3. Carpet must have Eco-worx backing.

4. Upon request, Tate will do Positile conversion on up to 9 carpet tiles for dealer evaluation. It is the dealer's responsibility to determine if the style is acceptable for their project.

5. Lighter face weight carpets tend to telegraph the Positile buttons more than heavier face weights. We will test lighter face weights, but a good rule of thumb is 16 to 18 ozs. Minimum.

It is important to maintain the module size during installation. It is critical that the grid size is not less than 24".

Care must be taken that the floor is not installed too tight or too loose. Panels should be easily removable without binding. Panel grid should be no less than 24' and no greater than 24' 1/8" when measured across 12 panels. This also causes a slight gap between carpet tiles ensuring a proper fit without edge bunching or excessive gaps. Proper installation of the access floor panels and Positile carpet tile are critical to ensuring the success of the installation and proper sizing of these gaps. Refer to the Tate's web-site for important guidelines (Positile Installation). Even when properly controlled, these gaps can affect the seaming of the installation and become more visually apparent especially when using light, solid colored tiles. Darker colors, patterned tiles, and quarter turning of tiles all are effective steps to minimize the visual impact of seams, however, they are a part of the inherent design of Positile and the customer must be informed in order to set their expectations: [Positile](#)

Positile Possibilities Shaw Products

Style #	Style Name	Backing type	Approval	Face Weight	Comments
5T003	Absorbed	Ecowerx	Yes	20 oz	Qualification 891 - Approved 09/12/2012
59327	Allure	Ecowerx	Yes	17 oz	Qualification 1149 - Approved 8/16/2018
5T004	Applied	Ecowerx	Yes	22oz	Qualification 961 - Approved 11/06/2014
5T064	Augment	Ecowerx	Yes	20 oz	Qualification 1129 - Approved 11/27/17
59340	Balance	Ecowerx	Yes	17 oz.	
5T448	Bisect	Ecowerx	Yes	16 oz	Qualification 1334 - Approved 2/17/23
59357	Blox	Ecowerx	Yes	24 oz.	
59554	Captivate	Ecowerx	Yes	19oz	Qualification 1050 - Approved 8/24/2015
59579	Catalyst	Ecowerx	Yes	17 oz	Qualification 842 - Approved 12/12/2011
5T124	Centric	Ecowerx	Yes	15 oz.	Qualification 1194 - Approved 8/21/19
59561	Charisma	Ecowerx	Yes	22 oz	Shaw (Lee Peacock) approved on 6/16/2010
5T081	Color Frame	Ecowerx	Yes	18 oz	Qualification 1215 Approved 2/14/20
59358	Color Play	Ecowerx	Yes	18 oz	
59342	Connect	Ecowerx	Yes	17 oz	
59326	Constellation	Ecowerx	Yes	24 oz	
59575	Diffuse	Ecowerx	Yes	18 oz	Qualification 848 - Approved 12/12/2011
5T071	Direction	Ecowerx	Yes	15 oz	Qualification 1111 - Approved 8/4/17
59576	Disperse	Ecowerx	Yes	16 oz	Qualification 772 - Approved 7/1/2010
5T265	Dream	Ecowerx	Yes	19 oz.	Qualification 1192 - Approved 7/22/19
5T142	Drift	Ecowerx	Yes	22 oz	Qualification 1169 - Approved 12/10/2018
5T040	Embark	Ecowerx	Yes	17 oz	Qualification 1347 - Approved 4/19/23
59343	Emotion	Ecowerx	Yes	17 oz	
5T268	Establish	Ecowerx	Yes	20 oz.	Qualification 1216 Approved 2/14/20
5T079	Field Tile	Ecowerx	Yes	17 oz	Qualification 1136 - Approved 5/7/2018
59455	Focus	Ecowerx	Yes	17oz	
59562	Glaze	Ecowerx	Yes	15 oz	Qualification 1103 - Approved 5/24/17
59329	Glimmer	Ecowerx	Yes	17 oz	Qualification 1148 - Approved 8/16/2018
59534	Gradient	Ecowerx	Yes	20oz	Qualification 817 - Approved 3/24/11
5T200	Gravel II	Ecowerx	NO	17 oz	Qualification 1217 - Rejected - Severe Telegraphing 2/5/20
5T065	Hype	Ecowerx	Yes	20 oz	Qualification 1128 - Approved 11/27/17
5T010	Infinite	Ecowerx	Yes	16 oz	Qualification 885 - Approved 8/20/12
59558	Intrigue	Ecowerx	Conditional	19 oz	Color Dependent
5T046	Kasuri	Ecowerx	Yes	22 oz	Qualification 1085 - Approved 2/22/17
59359	Kinetic	Ecowerx	Yes	18 oz	
5T263	Memory	Ecowerx	Yes	19 oz.	Qualification 1191 - Approved 7/22/19
59167	Merge	Ecowerx	Yes	18 oz	Qualification 898 - Approved 9/12/2012
59164	Minimal	Ecowerx	Yes	18 oz	Qualification 896 - Approved 9/12/2012
59466	Mirror Image	Ecowerx	Yes	19 oz	
5T123	Primary	Ecowerx	NO	13 oz.	Qualification 1292 Rejected 3/15/22 Excessive Telegraphing
5T324	Quad	Ecowerx	Yes	16 oz	Qualification 1385 - Approved 8/18/23
59387	Repartee	Ecowerx	Yes	22 oz	
5T069	Reverse	Ecowerx	Yes	15 oz.	Qualification 1091 - Approved 10/4/16
5T007	Sculpt	Ecowerx	NO	20 oz.	Qualification 1274 Rejected 1/26/22 Excessive Telegraphing
5T173	Sea Edge	Ecowerx	Yes	17 oz.	Qualification 1164 - Approved 12/10/18
5T172	Sea Tile	Ecowerx	Yes	17 oz.	Qualification 1165 - Approved 12/10/18
59328	Shine	Ecowerx	Yes	17 oz.	Qualification 886 - Approved 8/2/12

5T174	Sky	Ecoworx	Yes	17 oz.	Qualification 1316 - Approved 10/14/22
5T019	Tempt	Ecoworx	Yes	16 oz.	Qualification 1078 - Approved 1/8/16
5T005	Trace	Ecoworx	Yes	20 oz	Qualification 956 Approved 9/30/13
59563	Transparent	Ecoworx	Yes	15 oz.	Qualification 850 Approved 12/12/11
5T086	Vantage	Ecoworx	Yes	22 oz	Qualification 1167 Approved 12/10/18
5T009	Vast	Ecoworx	Yes	16 oz	Qualification 966 Approved 1/10/14
5T001	Vibrant	Ecoworx	Yes	20 oz	Qualification 889 Approved 9/12/12
5T002	Visible	Ecoworx	Yes	20 oz	Qualification 890 Approved 9/12/12
5T039	Wander	Ecoworx	Yes	17 oz	Qualification 1347 Approved 4/19/23

Positile Possibilities

Julie Industries ESD Products

Style #	Style Name	Backing type	Approval	Face Weight	Comments
N/A	Discovery Series	Ecoworx	Yes	24 oz.	
N/A	Presidential Series	Ecoworx	Yes	22.oz.	
N/A	Julie Lan 4.0	Ecoworx	Yes	22 oz.	Qualification 1043 - Approved 6/3/2015
N/A	Julie Lan 4.1	Ecoworx	Yes	22 oz.	
N/A	Julie Lan 4.2	Ecoworx	Yes	18 oz.	Qualification 1042 - Approved 6/3/2015
N/A	Julie Office Smart Daily Planner	Ecoworx	Yes	16 oz.	Qualification 1091 - Approved 2/22/17

Positile Possibilities

Shaw/Patcraft Products

Style #	Style Name	Backing type	Approval	Face Weight	Comments
I0574	Artful & Textured	Ecoworx	Yes	16 oz	Qualification 1264 Approved 9/1/21
I0574	Charcoal	Ecoworx	Yes	16 oz	Qualification 1394 Approved 2/16/24
I0204	Color Choice	Ecoworx	NO	30 oz	Qualification 1176 - Rejected - Severe Telegraphing
I0286	Earthen Weave	Ecoworx	Yes	19 oz	Qualification 1162 - Approved 12/10/2018
I0353	Homeroom V 3.0	Ecoworx	Yes	22 oz	Qualification 1248 Approved 6/14/21
I0519	Infrastructure	Ecoworx	Yes	16 oz	Qualification 1214 Approved 2/14/20
42KJY	Instinct	Ecoworx	Yes	15 oz	Qualification 1405 Approved 2/23/24
Z6476	Liquid	Ecoworx	Yes	17 oz	Qualification 1045 Approved 6/29/15
I0577	States of water	Ecoworx	Yes	20 oz	Qualification 1395 Approved 2/16/24
I0296	Tangible Hue	Ecoworx	NO	24 oz	Qualification 1176 - Rejected - Severe Telegraphing
I0578	Tidal	Ecoworx	Yes	20 oz.	Qualification 1353 Approved 4/28/23
I0302	Vivid Modular	Ecoworx	Yes	18 oz	Qualification 1046 Approved 8/7/15