

PEDESTAL SPECIFICATIONS

Pedestal Assembly

- Assembly from 2-7/8" (70mm) to 4" (100mm) FFH shall provide a 6,000 lb. axial load without permanent deformation.
- Assembly shall provide $\pm 1/2"$ (12mm) total adjustment with a minimum finished floor height of 2-7/8" (70mm).
- Overturning moment of 1,000 in./lbs. when Tate recommended pedestal adhesive is utilized on a clean unsealed concrete slab.
- All pedestal components and fasteners are completely electro zinc free.
- Zinc electroplating shall be prohibited on all pedestal components and fasteners.

Pedestal Head


- Die formed steel pedestal head with threaded core for height adjustment. Head and installed 2' (610mm) stringers shall provide full perimeter edge support for panel.
- Threaded core shall be 3/4" - 10 UNC.
- Pedestal head shall have tapped holes for engagement of stringer fasteners.
- Stringers shall be attached with 1/4" - 20 flat-head screws.

Pedestal Base

- Base to be at least 16" (100cm) square and galvanized steel.
- Solid steel stud shall be 3/4" - 10 UNC and projection welded to base plate.

Stringers

- Roll formed steel stringer will withstand 450 lb. mid-span load.
- Galvanized stringer construction to prevent corrosion. Zinc electroplating is prohibited.
- Stringer shall be 1-1/4" (31,75mm) deep x 3/4" (19mm) wide.
- Stringer grid pattern shall be 2/2' (610mm/610mm) only.



Perimeter

- Perimeter pedestal shall provide support for panels around columns, at walls, curbs and fascia.

