



Single Hinged Door

Specifications

- Pre-assembled panels allow for a simple and quick installation
- Perimeter compression gaskets efficiently seal and minimise air leakage
- Right or Left Hinged option (defined by which side of the door the handle is located as you look at the aisle from the outside)
- Multiwall option adheres to 2013 NFPA 75 flame spread and smoke development requirements Supports aisle widths of 4' to 6' (122m x 1.82m) (6' (1.82m) aisle is a wider door)
- No-threshold design prevents obstructions or tripping
- Sturdy aluminum framing
- Recessed Hinges allow for tighter joints
- Fully supported by floor with rack attachments for lateral stability.



Details

Weight:	75kg - Clear Polycarbonate
	61 kg - Multiwall polycarbonate
Dimensions:	182 cm (W) x 218 cm (H) x 9 cm (D)
	Max opening width: 91 cm

Included Components

Tate Single Hinged Door

Floor and rack Mounting hardware

Installation guide

Options

Panel Options

Clear polycarbonate

- Fully transparent
- ASTM D-635 listed
- 6mm thick with edge-sealing gaskets

Multiwall polycarbonate

- Semi-transparent
- Flame spread index <50
- Smoke development <450
- ASTM E-84 and ASTM D-635 listed
- UL 94 Listed 6mm thick with edge-sealing gaskets.

Aluminium Extrusion Finish Options

- Clear Anodised
- Black Anodised

Accessories

- Autocloser
- Push Plate (For use with Autocloser)
- Hold Open (for use with autocloser)



Single Hinged Door



Recessed Hinge design



Allows for tighter frame fit,
reducing air leakage



Tate Asia-Pacific Pty Ltd

E: info@tateapac.com

T: +61 2 9612 2300

W: tateglobal.com

Please note we reserve the right to change specification or design and supply products which may differ from those described and illustrated without notice and without liability. R: 01/2025