

## PEDESTAL SPECIFICATIONS

### Pedestal Assembly

- Assembly up to 60" (1500 mm) FFH shall provide a 6,000 lb. (2722 kg) axial load without permanent deformation.
- Assembly shall provide a 2" (50 mm) total adjustment with a floor height of 14" (350 mm) or greater.
- Standard finished floor heights from 14" (350mm) to 60" (1500 mm). For other finished floor heights please contact Tate. For seismic conditions, refer to seismic submittal details.
- Overturning moment of 1,000 in/lbs (5,600 cm/kgs) when Tate recommended pedestal adhesive is utilized.
- All pedestal components and fasteners are completely electro-zinc free.

### Pedestal Head


- 8 ga. die formed galvanized steel pedestal head with fillet welded stud with adjustment nut. Head and installed stringers shall provide full perimeter edge support for panel.
- Stringers shall be attached with 1/4" - 20 flat-head screws.
- Pedestal head shall be tapped for engagement of stringer screws.
- Steel stud shall be 3/4" - 10 UNC.
- Nut shall be 3/4" - 10 UNC with corrosion resistant coating.
- Stud shall provide an anti rotation feature when engaged with the pedestal base assembly

### Pedestal Base

- 1-1/4" schedule 40 steel pipe with 1.66" (42mm) O.D. fillet welded to 6" x 6" x 3/8" (150mm x 150mm x 9.5mm) steel base plate
- Base to be at least 36" (230 cm) square steel and shall have (4) 9/16" (14mm) diameter holes for mechanical fastening applications.
- Entire base to be shall have electrocoat finish

### Stringers

- Roll formed steel stringer shall be 2" (50 mm) deep X 3/4" (19 mm) wide and shall withstand 1250 lb. (567 kg.) mid-span load.
- Galvanized stringer construction to prevent corrosion. Zinc electroplating is prohibited.
- Stringer grid pattern shall be 4/4' (120cm / 120cm) basketweave.



### Perimeter

- Perimeter pedestal shall provide support for panels around columns, at walls, curbs and fascia.



Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or information that is found to be misleading or outdated. Suggestions for, or descriptions of, technical specifications and the end user or application of products are provided and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code.