

SPECIFICATIONS


- All steel construction
- Interchangeable with laminated ConCore and All Steel panels
- 25% open area without damper
- Panel size: 24 inches square
- Panel weight: 5.5 lb./ft²
- Protected from corrosion by Smoke Grey anti-static powder coat finish
- Design loads up to 1250lbs

UNDERSTRUCTURE OPTIONS

- ☐ 4' Bolted Stringer
- ☐ 2' Bolted Stringer
- ☐ 4' Box Stringer
- ☐ 2' Box Stringer

AIRFLOW CONTROL OPTIONS

- ☐ Slide Damper (factory installed)



TOP VIEW

Airflow Performance

Static Pressure (In. H ₂ O)	Air Volume (CFM)
0.02	395
0.04	470
0.05	525
0.06	560
0.08	620
0.10	750

Slide Damper


Air Volume w/ damper open (CFM)	Air Volume w/ damper closed (CFM)
280	10
330	30
350	40
380	50
405	50
520	55

FULL HARD COLD ROLLED STEEL TOP SHEET

POWDER COAT FINISH INSIDE & OUT


DRAW QUALITY STEEL BOTTOM PAN

Powder Coated Panel




HOT DIPPED GALVANIZED DAMPER

DAMPER ADJUSTS FROM TOP WITH ALLEN WRENCH



BOTTOM VIEW



BOTTOM VIEW WITH OPTIONAL SLIDE DAMPER



Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or information that is found to be misleading or outdated. Suggestions for, or descriptions of, technical specifications and the end user or application of products are provided and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code.