




TOP VIEW

SPECIFICATIONS

- All steel construction
- Interchangeable with laminated ConCore® and All Steel panels
- 32% open area without damper
- Panel size: 24 inches square
- Panel weight: 4.875 lb./ft²
- Patented intermingled airflow vanes for directional airflow
- Supports up to 1250lb load
- Capture index of 90%

UNDERSTRUCTURE OPTIONS


- ☐ 4' bolted stringer
- ☐ 4' box stringer

COATING OPTIONS

- ☐ Smoke Grey anti-static powder coat finish

AIRFLOW OPTIONS


- ☐ Single-zone Opposed Blade Damper (field mounted)



DIRECTIONAL MARKING

Airflow Performance

Static Pressure (In. H ₂ O)	Air Volume no damper (CFM)
0.02	535
0.04	735
0.05	820
0.06	880
0.08	1150
0.10	1285



Opposed Blade Damper

Air Volume w/ damper open(CFM)	Air Volume w/ damper closed(CFM)
505	195
725	260
785	280
875	305
1125	325
1250	355




Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or information that is found to be misleading or outdated. Suggestions for, or descriptions of, technical specifications and the end user or application of products are provided and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code.

FULL HARD COLD
ROLLED STEEL
TOP SHEET


POWDER COAT FINISH
INSIDE & OUT

ADDITIONAL OPENINGS IN
BOTTOM PAN

DRAW QUALITY STEEL
BOTTOM PAN



BOTTOM VIEW



**BOTTOM VIEW WITH OPTIONAL
OPPOSED BLADE DAMPER**



Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or information that is found to be misleading or outdated. Suggestions for, or descriptions of, technical specifications and the end user or application of products are provided and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code.