

Hollow Floor Pedestal M12

CLASS 5

- Bonding of the base plate to unfinished floors using Tate pedestal adhesive
- Top and bottom plates can be secured using a Tate pedestal adhesive
- Fix in place with Tate pedestal fixing adhesive as required



Pedestal		Test Results According to DIN EN 13213:2001	
Pedestal head	Top plate diameter 100 mm embossed Thickness 2 mm Pedestal tube 17 x 2 mm Tapered pedestal tube with thread M12 Top plate with tube centrally welded	Class	5
		Nominal point load	5 kN
		Ultimate load	≥ 10 kN
Depending on the respective Tate system			
Designation			
F1 - SHB M12 - SH			
F2 - SHB M12 - SH			
F3 - SHB M12 - SH			
F4 - SHB M12 - SH			
F5 - SHB M12 - SH			
F6 - SHB M12 - SH			
Material			
Steel, galvanised (transparent/bluish iridescent passivated)			

The adjustment ranges mentioned must be observed



Please scan the QR code or click [here](#) to go to the current product page.



Tate.

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany

T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-pedestal-m12-product-datasheet-en-de-v4 1/2026

