



ConCore® 2500/3000 Access Floor Panel With Bolted Stringer Understructure System

SECTION 09 69 00 ACCESS FLOORING

PART 1 - GENERAL

1.1 Section Includes

- A. Work of this section includes, but is not limited to: access floor panels, floor coverings, understructure and various electrical, data and communication accessories.

1.2 Related Sections

- A. Concrete sealer shall be compatible with pedestal adhesive, see Division 3.
- B. See Division 26 Section "Grounding and Bonding for Electrical Systems" for connection to ground of access flooring understructure. Note: The electrical engineer or contractor shall determine requirements for grounding and the electrical contractor shall provide the necessary labor and materials to electrically connect the access flooring to the building ground if it is required.

1.3 Environmental Conditions for Storage and Installation

- A. Area to receive and store access floor materials shall be enclosed and maintained at ambient temperatures between 35° to 95° F and relative humidity levels between 20% to 80%. All floor panels shall be stored at ambient temperature between 50° to 90° F for at least 24 hours before installation begins. All areas of installation shall be enclosed and maintained at ambient temperature between 50° to 90° F and at relative humidity levels between 20% to 80%, and shall remain within these environmental limits throughout occupancy.

1.4 References

- A. CISCA (Ceilings & Interior Systems Construction Association) - "Recommended Test Procedures for Access Floors" shall be used as a guideline when presenting load performance product information.

1.5 Performance Certification

- A. Product tests shall be witnessed and certified by independent engineering and testing laboratory based in the U.S. with a minimum of five years experience testing access floor components in accordance CISCA "Recommended Test Procedures for Access Floors".

1.6 Country-of-Origin and Product Marking

- A. Access floor materials shall comply with the provisions outlined in FAR Subpart 25.2 – Buy American Act – Construction Materials.





- B. Floor panels shall be permanently marked with manufacturer's name, product identification, manufacturing date and country-of-origin. Removable Product ID stickers are not acceptable.

1.7 Performance Requirements

- A. **Design Load:** Panel supported on actual understructure system shall be capable of supporting a point load of 3000 lbs. applied on a one square inch area at any location on the panel without experiencing permanent set in excess of 0.010 inches as defined by CISCA. The loading method used to determine design (allowable) load shall be in conformance with CISCA Concentrated Load test method but with panel tested on actual understructure instead of steel blocks.
- B. **Safety Factor:** Panel supported on actual understructure system shall withstand a point load of no less than (2) two times its design load rating on a one square inch area anywhere on the panel without failure when tested in accordance with CISCA A/F, Section 2, "Ultimate Loading". Failure is defined as the point at which the system will no longer accept the load.
- C. **Ultimate Load:** Panel supported on actual understructure system shall be capable of supporting a point load of at least 6000 lbs. applied through a load indenter on a one square inch area at any location on the panel without failure (i.e. minimum safety factor if 2) when tested in accordance with CISCA A/F, Section 2, "Ultimate Loading".
- D. **Rolling Load:** Panel supported on actual understructure system shall be able to withstand the following rolling loads at any location on the panel without developing a local and overall surface deformation greater than 0.040 inches when tested in accordance with CISCA A/F Section 3, "Rolling Loads". Note: wheel 1 and wheel 2 tests shall be performed on two separate panels.

CISCA Wheel 1: Size: 3" dia x 1 13/16" wide Load: 2700 lbs. Passes: 10
CISCA Wheel 2: Size: 10" dia x 4" wide Load: 2400 lbs. Passes: 10,000
- E. **Impact Load:** Panel and supporting understructure (the system) shall be capable of supporting an impact load of 300 lbs. dropped from a height of 36 inches onto a one square inch area (using a round or square indenter) at any location on the panel when tested in accordance with CISCA A/F, Section 8, "Drop Impact Load Test".
- F. **Flammability:** Panel shall meet *Class A* Flame spread requirements for flame spread and smoke development. Tests shall be performed in accordance with ASTM-E84-1998, Standard Test Method for Surface Burning Characteristics for Building Materials.
- G. **Recycled Content:** Panel and understructure system shall be required to have a minimum post-consumer recycled content of 18% and a minimum total recycled content of 49%.





- H. **Axial Load:** Pedestal support assembly shall provide a 6000 lb. axial load without permanent deformation when tested in accordance with CISC A/F, Section 5, “Pedestal Axial Load Test”.
- I. **Overtopping Moment:** Pedestal support assembly shall provide an average overturning moment of 1000 in-lbs. when glued to a clean, sound, uncoated concrete surface when tested in accordance with CISC A/F, Section 6, “Pedestal Overturning Moment Test”.
- J. **Stringer Concentrated Load:** Stringer shall be capable of withstanding a concentrated load of 1250 lbs. placed in its midspan on a one square inch area using a round or square indenter without exceeding a permanent set of 0.010” after the load is removed when tested in accordance with CISC A/F, Section 4, “Stringer Load Testing”.

1.8 **Design Requirements:**

- A. Access floor system, where indicated on the design documents, shall consist of modular and removable fully encased cementitious filled welded steel panels supported on all four edges by structural steel members which are designed to bolt onto adjustable height pedestal assemblies forming a modular grid pattern.
- B. Panel shall be easily removed by one person with a suction cup lifting device and shall be interchangeable except where cut for special conditions.
- C. Quantities, finished floor heights (FFH) and location of accessories shall be as specified on the contract drawings.

1.9 **Submittals for Review**

- A. Detail sheets, for each proposed product type, which provide the necessary information to describe the product and its performance.
- B. Test reports, certified by an independent testing laboratory with a minimum of five years experience testing access floor components in accordance with CISC Recommended Test Procedures, certifying that component parts perform as specified.

1.10 **Submittals for Information**

- A. Manufacturer’s installation instructions and guidelines.
- B. Manufacturer’s Owner Manual outlining recommended care and maintenance procedures.

PART 2 - PRODUCTS

2.1 **Manufacturers**

- A. Access floor system shall be as manufactured by Tate Access Floors, Inc. and shall consist of ConCore® 3000 access floor panel supported by a bolted stringer understructure system.





- B. Alternative products shall meet or exceed all requirements as indicated herein and must receive prior written approval by the architect or designer.
- C. Access floor manufacture shall be ISO9001: 2015 certified demonstrating it has a robust and well documented quality management system with continuous improvement goals and strategies.
- D. Access floor manufacturer's facilities shall be ISO14001:2015 certified demonstrating that they maintain an environmental management system.
- E. Access floor manufacturer's facilities shall be OHSAS 18001:2018 certified demonstrating that they maintain an Occupational Health and Safety Management system.

2.2 Support Components

Pedestals:

- A. Pedestal assemblies shall be corrosive resistant, all steel welded construction, and shall provide an adjustment range of +/- 1" for finished floor heights 6" or greater. Zinc electroplating shall be prohibited on all pedestal components, including head plate, threaded rod, adjustment nut, pedestal tube, base plate, and all fasteners.
- B. Pedestal assemblies shall provide a means of leveling and locking the assembly at a selected height, which requires deliberate action to change height setting and prevents vibration displacement.
- C. Hot dip galvanized steel pedestal head shall be welded to a threaded rod which includes a specially designed adjusting nut. The nut shall provide location lugs to engage the pedestal base assembly, such that deliberate action is required to change the height setting.
- D. Threaded rod shall provide a specially designed anti-rotation device, such that when the head assembly is engaged in the base assembly, the head cannot freely rotate (for FFH of 7" or greater and Types 1A and 2B square tube bases only). Note: This prevents the assembly from inadvertently losing its leveling adjustment when panels are removed from the installation during use.
- E. Hot dip galvanized pedestal base assembly shall consist of a formed steel plate with no less than 16 inches of bearing area, welded to a 7/8" square steel tube and shall be designed to engage the head assembly.

Stringers:

- A. Roll formed stringers shall be 2" deep by 3/4" wide and shall support each edge of panel.
- B. Steel stringer shall have conductive galvanized coating. Zinc electroplating shall be prohibited on stringers and stringer fasteners.
- C. Stringers shall be individually and rigidly fastened to the pedestal with one machine screw for each foot of stringer length. Bolts shall provide positive electrical contact





between the stringers and pedestals. Connections depending on gravity or spring action are unacceptable.

- D. Stringer grid shall be 4' stringers in a basketweave configuration ensuring maximum lateral stability in all directions.

2.3 Panel Components

Floor Panels:

- A. Panels shall consist of a top steel sheet welded to a formed steel bottom pan filled internally with a lightweight cementitious material. Mechanical or adhesive methods for attachment of the steel top and bottom sheets are unacceptable.
- B. Floor panels shall be protected from corrosion by electro-deposited epoxy paint. The use of zinc electroplating shall be prohibited.
- C. Cementitious fill material shall be totally encased within the steel welded shell except where cut for special conditions. Note: This greatly reduces the potential for dust in the environment from exposed cement materials.

2.4 Accessories

- A. Provide manufacturer's standard steps, ramps, fascia plate, perimeter support, and grommets where indicated on the contract drawings.
- B. Provide _____ spare floor panels and _____ square feet of understructure systems for each type used in the project for maintenance stock. Deliver to project in manufacturer's standard packaging clearly marked with the contents.
- C. Provide _____ panel lifting devices.
- D. When applicable provide manufacturer's standard underfloor air systems components (including grilles and diffusers) where indicated on the contract drawings.

2.5 Fabrication Tolerances

- A. Floor panel flatness measured on a diagonal: +/- 0.035"
- B. Floor panel flatness measured along edges: +/- 0.025"
- C. Floor panel width or length of required size: +/- 0.010"
- D. Floor panel squareness tolerance: +/- 0.015"

PART 3 – EXECUTION

3.1 Preparation

- A. Examine structural subfloor for unevenness, irregularities and dampness that would affect the quality and execution of the work. Do not proceed with installation until structural floor surfaces are level, clean, and dry as completed by others.





- B. Concrete sealers, if used, shall be identified and proven to be compatible with pedestal adhesive. Verify that adhesive achieves bond to slab before commencing work.
- C. Verify dimensions on contract drawings, including level of interfaces including abutting floor, ledges and doorsills.
- D. The General Contractor shall provide clear access, dry subfloor area free of construction debris and other trades throughout installation of access floor system.
- E. Area to receive and store access floor materials shall be enclosed and maintained at ambient temperatures between 35° to 95° F and a minimum relative humidity of 20%. At least 24 hrs. before installation begins, all floor panels shall be stored at ambient temperatures between 50° to 90° F and relative humidity levels between 20% to 80% and shall remain within these environmental limits throughout occupancy.

3.2 Installation

- A. Pedestal locations shall be established from approved shop drawings so that mechanical and electrical work can be installed without interfering with pedestal installation.
- B. Installation of access floor shall be coordinated with other trades to maintain the integrity of the installed system. All traffic on access floor shall be controlled by access floor installer. No traffic but that of access floor installers shall be permitted on any floor area for 24 hours to allow the pedestal adhesive to set. Access floor panels shall not be removed by other trades for 72 hours after their installation.
- C. Floor system and accessories shall be installed under the supervision of the manufacturer's authorized representative and according to manufacturer's recommendations.
- D. No dust or debris producing operations by other trades shall be allowed in areas where access floor is being installed to ensure proper bonding of pedestals to subfloor.
- E. Access floor installer shall keep the subfloor broom clean as installation progresses.
- F. Partially complete floors shall be braced against shifting to maintain the integrity of the installed system where required.
- G. Additional pedestals as needed shall support panels where floor is disrupted by columns, walls, and cutouts.
- H. Understructure shall be aligned such that all uncut panels are interchangeable and fit snugly but do not bind when placed in alternate positions.
- I. Finished floor shall be level, not varying more than 0.062" in 10 feet or 0.125" overall.
- J. Inspect system prior to application of floor covering and replace any floor panels that are cracked, broken and structurally damaged and do not comply with specified requirements.





K. Acceptance: General contractor shall accept floor in whole or in part prior to allowing use by other trades.

End



Rev: 09/22/25

ECN: 16502

© 2025 Tate Access Floors, Inc

Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or for information that is found to be misleading or outdated. Suggestions for, or description of, technical specifications and the end use or application of products are provided in good faith and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code above.

www.Tateinc.com

