

## SPECIFICATIONS

- All steel construction
- Interchangeable with laminated ConCore and All Steel panels
- 25% open area without damper
- Panel size: 24 inches square
- Panel weight: 27 lbs. (without damper)
- Protected from corrosion by an epoxy paint finish

## UNDERSTRUCTURE OPTIONS

4' Bolted Stringer       4' Box Stringer

## COVERING OPTIONS

Tile factory laminated with integral trim edge


.040" HPL \_\_\_\_\_ (color) \_\_\_\_\_

1/16" HPL \_\_\_\_\_ (color) \_\_\_\_\_


## AIRFLOW CONTROL OPTIONS

Slide Damper (factory installed)

## Laminated Panel With Integral Trim Edge



## TOP VIEW




## Airflow Performance

Static Pressure (In. H <sub>2</sub> O)	Air Volume (CFM)
0.02	370
0.04	440
0.05	480
0.06	515
0.08	575
0.10	700

## Slide Damper

Air Volume w/ damper open (CFM)	Air Volume w/ damper closed (CFM)
260	10
300	20
340	40
350	50
375	55
490	60



Tate reserves the right to amend product information without prior notice. Care has been taken to ensure that the contents of this publication are accurate, but Tate, its parent company and its subsidiary companies do not accept responsibility for errors or information that is found to be misleading or outdated. Suggestions for, or descriptions of, technical specifications and the end user or application of products are provided and must be verified prior to use. To ensure you are viewing the most recent and accurate product information, please scan the QR code.