


LK 1-600-19 Fermacell

LOAD CLASS 1

The Tate Ecoprimo hollow floor system LK1-600/19 was designed for a load according to DIN EN 13213: 2001, load class 1. They are used in rooms where there is a high cable density for electrical supply or data transfer and high flexibility for use is required, such as in offices, ticket halls, exhibition rooms or libraries. Due to the excellent sound improvement properties, the use in multi-storey buildings is often possible without additional requirements for the shell construction.



Special features

Column spacing area	600 mm
Column spacing edge	600 mm
Scree thickness area	38 mm
Scree thickness edge	38 mm
System panel thickness	19 mm
System plate dimensions	1200 x 600 mm

Substructure

Pedestal	Height adjustable steel pedestals M12 (F1 - F6), for higher constuctions M16/M20
----------	--

Statics according to DIN EN 13213: 2001

Load class	1
Working load	2 kN
Safety factor	2

Fire protection according to DIN 4102-2: 1977

Building material class 4102	non-flammable
Fire-resistance class	F30 up to clear heights of 300 mm

Sound insulation according to DIN EN ISO 10140: 2021, DIN EN ISO 10848: 2018 and DIN EN ISO 140: 2005

Impact sound reduction (horizontal) (Ln,f,w,P)

without covering	75 dB
with covering	51 dB

Airborne sound reduction (Dn,f,w,P)

without covering	56 dB
------------------	-------

Impact sound reduction (vertical) (ΔLw,P)

without covering	19 dB
with covering	25 dB
with bottom sound pad, without covering	*26 dB
with top sound pad, without covering	**24 dB
with top PE-sound pad, without covering	21 dB

Note:

It should be noted that the use of sound pads can impact the system's rigidity. As a result, limitations with regard to the aforementioned load capacity must be taken into account.

Depending on the covering used, the sound values may differ. According to the manufacturer's specifications, the impact sound reduction resulting from the floor coverings ranges between $\Delta Lw: 18-30$ dB. If you require detailed information regarding the sound values, please feel free to contact the technical department.

*Sound pad ø 60 x 5 mm

**Sound pad ø 100 x 2 mm



Please scan the QR code or click [here](#) to go to the current product page.



Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany
T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.
Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-ecoprimo-lk1-600-19-fermacell-datasheet-en-de-v2 1/2026



LK 1-600-19 Fermacell

The Tate hollow floor system Ecoprimo LK 1-600/19 was designed for a load according to DIN EN 13213: 2001, load class 1. This classification provides for a working load of 2,000 N and a breaking load of $\geq 4,000$ N.

Static measures



For this load case, no special static measures in the construction are necessary. All supports can be installed with a maximum spacing of 600 mm in the surface as well as in the edge area. Additional supports must be installed in the corner areas for static reasons.

Increased sound insulation requirements

If increased sound insulation is required, special insulation panels can be used in the support area.

Fire protection

The system is tested according to ABP F30 according to DIN 4102-2: 1977 (clear height up to 300 mm with appropriate substructure).



Please scan the QR code or click [here](#) to go to the current product page.

Tate.

Tate Global GmbH

Zum Stadion 4, 63808 Haibach, Germany
T: +49 (0) 6021 63949-0 E: infoDE@tateglobal.com W: tateglobal.com/de

© 2025 Tate Global GmbH.

Tate Global GmbH reserves the right to amend or add to the product specifications without prior notice as part of our commitment to continuous improvements and the observance of legal changes.

tate-ecoprimo-lk1-600-19-fermacell-datasheet-en-de-v2.1/2026

 **PLANET
PASSIONATE**

#planetpassionate