

GENERAL INFORMATION

- Pre-assembled panels allow for a simple and quick installation
- Perimeter compression gaskets efficiently seal and minimize air leakage
- Right or Left Hinged option (defined by which side of the door the hinge is located as you look from the outside)
- Supports aisle widths of 4' to 6' (1.22 m to 1.83 m)
- No-threshold design prevents obstructions or tripping
- Sturdy aluminum framing
- Recessed hinges allow for tighter joints
- Fully supported by floor with rack attachments for lateral stability

Weights

- 165 lbs (74.8 kg) -- Clear Polycarbonate
- 135 lbs (61.2 kg) -- Multiwall Polycarbonate

Dimensions

- _____ Width x _____ Height X 3.6" (9.1 cm) depth
- _____ Opening Width

OPTIONS

- ☐ Clear polycarbonate
 - Fully transparent
 - 6mm thick with edge sealing gaskets
- ☐ Multiwall polycarbonate: ASTM E84, Class-A
 - Semi-transparent
 - 8mm thick
- ☐ Dibond
 - Opaque Black ACM
 - 3mm thick
- ☐ Aluminum extrusion finish options
 - Black
 - Grey
 - White


OPTIONS (CONTINUED)

Accessories

- Autocloser
- Push Plate (for use with Autocloser)
- Hold open (for use with Autocloser)

INCLUDED COMPONENTS

- Single Hinged Door
- Floor and rack mounting hardware
- Installation guide



Recessed Hinge design

Allows for tighter frame fit, reducing air leakage

